

YS1CLBOX, Compression Splice, 1 AWG, Copper, Standard Barrel

By Burndy
Catalog # YS1CLBOX



1 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, GREEN Color Code, 11 or 375 Die Index.

Application

Wire Splice

General

Catalog Number	YS1CLBOX
Color Code	Green
Connector Type	STANDARD BARREL
Die Index	11
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810555002
UPC 12 Digit	7818105550022

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.06 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Strip Length inch	15/16

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor - Material	COPPER
Conductor Size	1 AWG
Conductor Type	CODE
Wire Size	3/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1

Product Assets

- [3D Models - YS1CLBOX_MODEL-IGES](#)
- [3D Models - YS1CLBOX_MODEL-PDF](#)
- [3D Models - YS1CLBOX_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd022390_1](#)
- [Specifications - YS1CLBOX](#)



A Hubbell brand