

# Compression Splice

By Burndy  
Catalog # [YS1CPULL](#)

Hylink Cu compression long barrel code splice tubing, Beveled entry, #1STR kcmil.Cu, 600V-35KV, Tin plated, Green, 11 or 375 Index.



## Application

Wire Splice

## General

Color Code	Green
Connector Type	LONG BARREL
Die Index	11
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Bright
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	YS
UPC	781810090084
UPC 12 Digit	7818100900844

## Dimensions

Dimension - B Length inch	1.35 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.06 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	4/O AWG
Conductor - Copper Str Size Range	1 AWG
Conductor - Material	COPPER
Conductor Size	1 AWG
Conductor Type	CODE
Wire Size	4/O AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	20
Minimum Pack Quantity	1

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 30018849](#)