

Compression Splice

By Burndy
Catalog # [YS25PULL](#)

Hylink Cu compression long barrel code splice tubing, Beveled entry, 1/0 STR kcmil.Cu, 600V-35KV, Tin plated, Pink, 12 or 348 Index.



Application

Wire Splice

General

Color Code	Pink
Connector Type	LONG BARREL
Die Index	12
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Bright
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	YS
UPC	781810105498
UPC 12 Digit	7818101054988

Dimensions

Dimension - B Length inch	1.35 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.08 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	700 KCMIL;750 KCMIL
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE
Wire Size	700 KCMIL; 750 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1

Product Assets

[3D Models - YS25PULL_MODEL-PDF](#)
[3D Models - YS25PULL_MODEL-IGES](#)
[3D Models - YS25PULL_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 30018849](#)