



YS26FXLTCKITC, Compression Splice Kit with Clear Heat Shrink, 2/0 Flex G,H,I,K,M, DLO, 2/0 AWG Cu

By Burndy
Catalog # [YS26FXLTCKITC](#)



2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink Black Color Code, 13 Die Index.

Application

Wire Splice

General

Catalog Number	YS26FXLTCKITC
Color Code	Black
Color Code - Side A	Black
Color Code - Side B	Black
Connector Type	STANDARD BARREL KITS
Die Index	13
Die Index Run Side	13
Die Index Tap Side	13
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810344125
UPC 12 Digit	7818103441255

Dimensions

Dimension - B Length inch	1.10 in
Dimension - L Length Overall mm	66.5 mm
Dimension - Length BB inch	1.10 in
Dimension - Length Overall inch	2.62 in
Dimension - Strip Length inch	1.1

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Flex G Size A	2/0 AWG
Conductor - Copper Flex G Size B	2/0 AWG
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Copper Flex H Size A	2/0 AWG
Conductor - Copper Flex H Size B	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG
Conductor - Copper Flex I Size A	2/0 AWG
Conductor - Copper Flex I Size B	2/0 AWG
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex K Size A	2/0 AWG
Conductor - Copper Flex K Size B	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor - Copper Flex M Size A	2/0 AWG
Conductor - Copper Flex M Size B	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 WG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	1080

Product Assets

[3D Models - YS26FXLTCKITC_MODEL-PDF](#)
[3D Models - YS26FXLTCKITC_MODEL-IGES](#)
[3D Models - YS26FXLTCKITC_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10101349](#)
[Specifications - YS26FXLTCKITC](#)



A Hubbell brand