



## YS26LBOX, Cu Compression Splice, Standard Barrel, 2/0 AWG

By Burndy  
Catalog # [YS26LBOX](#)

2/0 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated,  
UL/CSA, 90°C, Up to 35kV, BLACK Color Code, 13 Die Index.



## Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

## Application

Wire Splice

## General

Catalog Number	YS26LBOX
Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810556252
UPC 12 Digit	7818105562522

## Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - L Length Overall mm	55 mm
Dimension - Length Overall inch	2.17 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Strip Length inch	1 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Size	900 KCMIL
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE
Wire Size	900 KCMIL

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1

## Product Assets

[3D Models - YS26LBOX\\_MODEL-PDF](#)  
[3D Models - YS26LBOX\\_MODEL-IGES](#)  
[3D Models - YS26LBOX\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - sd022390\\_1](#)  
[Specifications - YS26LBOX](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-YS26LBOX-SPEC-EN | REV 1/2025