



Compression Splice

By Burndy
Catalog # YS28LBRBOX

4/0 AWG CU, Standard Barrel, Internal Chamfer, Bare Non-Plated, UL/CSA, 90°C, Up to 35kV, PURPLE Color Code, 15 Die Index.



Application

Wire Splice

General

Color Code	Purple
Connector Type	STANDARD BARREL
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Bare
Material	COPPER
Plated	N
Plating Type	Unplated
Trade Name	HYLINK™
UPC	781810420638
UPC 12 Digit	7818104206388

Dimensions

Dimension - B Length inch	1.00 in
Dimension - Inside Diameter inch	0.55 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.32 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Strip Length inch	1-1/16

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Size	571.1 Kcmil
Conductor - Copper Flex H Size	571.1 Kcmil
Conductor - Copper Flex I Size	571.1 Kcmil
Conductor - Copper Flex K Size	571.1 Kcmil
Conductor - Copper Flex M Size	571.1 Kcmil
Conductor - Copper Str Compact Size	4/0
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Navy Size Range	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD022390](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YS28LBRBOX-SPEC-EN | REV 8/2023