

Compression Splice

By Burndy
Catalog # [YS29L](#)



Hylink Cu compression standard barrel code splice tubing,
Beveled entry, 250 kcmil .Cu, 600V-35KV, Tin plated.

Application

Wire Splice

General

Color Code	Yellow
Connector Type	STANDARD BARREL
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810070284
UPC 12 Digit	7818100702844

Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - L Length Overall mm	62 mm
Dimension - Length Overall inch	2.46 in
Dimension - Strip Length inch	1-1/8

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Compact Size	250
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	14400

Product Assets

[3D Models - YS29L_MODEL-STEP](#)
[3D Models - YS29L_MODEL-IGES](#)
[3D Models - YS29L_MODEL-PDF](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD022390-01](#)