

YS2CAT, Aluminum - Compression Splice

By Burndy
Catalog # [YS2CAT](#)

Al Comp Splice, High Voltage Uninsul, Tapered Ends, #2 Str(Al), 35 KV, 4.00" L, 348 Index.



General

Catalog Number	YS2CAT
Color Code	Pink
Connector Type	Splice
Die Index	348
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810001356

Dimensions

Dimension - B Length inch	1.58 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.00 in
Dimension - Outside Diameter inch	0.53 in
Dimension - Pad Width inch	1.93 in
Dimension - Strip Length inch	2 1/4

Conductor Related

Conductor - AL Str Size	2 AWG
-------------------------	-------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	19600

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YS-AT_LineArt](#)
[Sales Drawings - SC..025626-01](#)
[Specifications - YS2CAT](#)