

## YS2CLBOX, Cu Compression Splice, Standard Barrel, 2 AWG

By Burndy  
Catalog # [YS2CLBOX](#)

2 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated,  
UL/CSA, 90°C, Up to 35kV, BROWN Color Code, 10 Die Index



### Application

Wire Splice

### General

Catalog Number	YS2CLBOX
Color Code	Brown
Connector Type	STANDARD BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810555255
UPC 12 Digit	7818105552555

### Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Strip Length inch	15/16

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE
Wire Size	#2 AWG

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1

### Product Assets

- [3D Models - YS2CLBOX\\_MODEL-STEP](#)
- [3D Models - YS2CLBOX\\_MODEL-IGES](#)
- [3D Models - YS2CLBOX\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd022390\\_1](#)
- [Specifications - YS2CLBOX](#)



A Hubbell brand