



Compression Splice

By Burndy
Catalog # [YS2CPULL](#)

Hylink Cu compression long barrel code splice tubing, Beveled entry, #2 STR kcmil.Cu, 600V-35KV, Tin plated, Brown, 10 Index.



Application

Wire Splice

General

Color Code	Brown
Connector Type	LONG BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Bright
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	Type YS
UPC	781810090190
UPC 12 Digit	7818100901900

Dimensions

Dimension - B Length inch	1.22 in
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.82 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 30018849](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YS2CPULL-SPEC-EN | REV 5/2024