



# Compression Splice

By Burndy  
Catalog # [YS30FX](#)

250 KCMIL G&H, 250 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, YELLOW Color Code, 16 Die Index.



### Application

Wire Splice

### General

Color Code	Yellow
Connector Type	LONG BARREL
Construction Material - Main	Copper
Die Index	16
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS
UPC	621945624122

### Dimensions

Dimension - B Length inch	1.95
Length	4.33 in

### Electrical Ratings

Voltage Rating	35 kV
----------------	-------

### Conductor Related

Conductor - Copper Flex G Size	250 KCMIL
Conductor - Copper Flex G Size Range	250 KCMIL
Conductor - Copper Flex H Size	250 KCMIL
Conductor - Copper Flex H Size Range	250 KCMIL
Conductor - Copper Str Size	250 KCMIL
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	FLEX
Wire Size	250 KCMIL

### Certifications And Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Brochures - Burndy\\_Copper Flex Splices - Long Barrel\\_Brochure](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50117138](#)



A proud member of the Hubbell Family.