



# Compression Splice

By Burndy  
Catalog # [YS30LFX](#)

250 KCMIL G,H, 250 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, YELLOW Color Code, 16 Die Index.



### Application

Wire Splice

### General

|                              |                      |
|------------------------------|----------------------|
| Color Code                   | Yellow               |
| Connector Type               | STANDARD BARREL      |
| Construction Material - Main | Copper               |
| Die Index                    | 16                   |
| EU RoHS Indicator            | Contact Manufacturer |
| Finish Type                  | Tin-Plated           |
| Material                     | COPPER               |
| Sub Brand                    | HYLINK               |
| Trade Name                   | HYLINK™              |
| Type                         | YS                   |
| UPC                          | 621945623989         |

### Dimensions

|                           |         |
|---------------------------|---------|
| Dimension - B Length inch | 1.01    |
| Length                    | 2.46 in |

### Electrical Ratings

|                |       |
|----------------|-------|
| Voltage Rating | 35 kV |
|----------------|-------|

### Conductor Related

|                                      |           |
|--------------------------------------|-----------|
| Conductor - Copper Flex G Size       | 250 KCMIL |
| Conductor - Copper Flex G Size Range | 250 KCMIL |
| Conductor - Copper Flex H Size       | 250 KCMIL |
| Conductor - Copper Flex H Size Range | 250 KCMIL |
| Conductor - Copper Str Size          | 250 KCMIL |
| Conductor - Material                 | COPPER    |
| Conductor Size                       | 250 KCMIL |
| Conductor Type                       | FLEX      |
| Wire Size                            | 250 KCMIL |

### Certifications And Compliance

|                              |              |
|------------------------------|--------------|
| Certification - CSA Approved | CSA          |
| Certification - cULus        | NO           |
| Industry Standard(s)         | UL 486A-486B |

### Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 6 |
|-----------------|---|

### Product Assets

[Brochures - Burndy\\_Copper Flex Splices - Standard Barrel\\_Brochure](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50117136](#)



A proud member of the Hubbell Family.