



Compression Splice

By Burndy
Catalog # [YS31LFX](#)

250 KCMIL I,K,M, 262 DLO, 250 AWG CU, Standard Barrel,
Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV,
WHITE Color Code, 17 Die Index.



Application

Wire Splice

General

Color Code	White
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	17
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS
UPC	621945623866

Dimensions

Dimension - B Length inch	1.07
Length	2.6 in

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper DLO Size	262 KCMIL
Conductor - Copper DLO Size Range	262 KCMIL
Conductor - Copper Flex I Size	250 KCMIL
Conductor - Copper Flex I Size Range	250 KCMIL
Conductor - Copper Flex K Size	250 KCMIL
Conductor - Copper Flex K Size Range	250 KCMIL
Conductor - Copper Flex M Size	250 KCMIL
Conductor - Copper Str Size	250 KCMIL
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	FLEX
Wire Size	250 KCMIL

Certifications And Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

Logistics

Carton Quantity	60
-----------------	----

Product Assets

[Brochures - Burndy_Copper Flex Splices - Standard Barrel_Brochure](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50117136](#)



A proud member of the Hubbell Family.