

YS32, Cu Compression Splice, Long Barrel, 400 kcmil

By Burndy Catalog # YS32



Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

General

Catala a Numahan	VC70
Catalog Number	YS32
Color Code	Blue
Connector Type	LONG BARREL
Die Index	19
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Υ
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Туре	YS, Long Barrel
UPC	781810508404
UPC 14 Digit GTIN	00781810508404

Dimensions

Dimension - B Length inch2.08 inDimension - L Length Overall117 mmmmDimension - Length Overall4.62 ininchDimension - Strip Length inch2-1/16

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV



Conductor Related

Conductor - Copper Str Navy	400 (127) Navy
Size	
Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size	400 kcmil
Range	
Conductor - Material	COPPER
Conductor Size	400 KCMIL
Conductor Type	CODE
Wire Size	400 kcmil

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	СМ
Status	
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1

Product Assets

3D Models - YS32_MODEL-IGES
3D Models - YS32_MODEL-STEP
3D Models - YS32_MODEL-PDF
Catalogs - BURNDY Master Catalog - Section C - Compression
Connections
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - SD007774-01
Specifications - YS32



A Hubbell brand

@2025 Hubbell Incorporated. All rights reserved BRDY-YS32-SPEC-EN | REV 3/2025