



Compression Splice

By Burndy
Catalog # [YS32LFX](#)

300 KCMIL G,H,I,K,M, 313 DLO, 300 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, RED Color Code, 18 Die Index.



Application

Wire Splice

General

Color Code	Red
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	18
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS
UPC	621945623996

Dimensions

Dimension - B Length inch	1.14
Length	2.74 in

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper DLO Size	313 KCMIL
Conductor - Copper DLO Size Range	313 KCMIL
Conductor - Copper Flex G Size	300 KCMIL
Conductor - Copper Flex G Size Range	300 KCMIL
Conductor - Copper Flex H Size	300 KCMIL
Conductor - Copper Flex H Size Range	300 KCMIL
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex I Size Range	300 KCMIL
Conductor - Copper Flex K Size	300 KCMIL
Conductor - Copper Flex K Size Range	300 KCMIL
Conductor - Copper Flex M Size	300 KCMIL
Conductor - Copper Str Size	300 KCMIL
Conductor - Material	COPPER
Conductor Size	300 KCMIL
Conductor Type	FLEX
Wire Size	300 KCMIL

Certifications And Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Brochures - Burndy_Copper Flex Splices - Standard Barrel_Brochure](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50117136](#)



A proud member of the Hubbell Family.

