



## YS34AT, Aluminum - Compression Splice

By Burndy  
Catalog # [YS34AT](#)



High Voltage Uninsulated Al Tube Compression Splice, 500 kcmil Al Cable, 7.79" L.

### General

Catalog Number	YS34AT
Color Code	Pink
Connector Type	Splice
Die Index	300
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Crimps Required	6
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810757611

### Dimensions

Dimension - B Length inch	3.39 in
Dimension - L Length Overall mm	198 mm
Dimension - Length Overall inch	7.79 in
Dimension - Outside Diameter inch	1.32 in
Dimension - Pad Width inch	3.79 in
Dimension - Strip Length inch	4 1/8

### Conductor Related

Conductor - AL Str Size	500 kcmil
-------------------------	-----------

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	3600

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YS-AT\\_LineArt](#)
- [Sales Drawings - SC..025626-01](#)
- [Specifications - YS34AT](#)