

Compression Splice

By Burndy
Catalog # [YS34LG3BR](#)



Copper Compression HYLINK™, Splice, Standard, Unplated.

Application

Wire Splice

General

Color Code	Red
Connector Type	STANDARD BARREL
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Bare
Material	COPPER
Plated	Y
Plating Type	Tin - Bright
Trade Name	HYLINK™
UPC	781810047903
UPC 12 Digit	7818100479033

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.91 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Strip Length inch	1-7/16

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Compact Size	350 kcmil
Conductor - Copper Str Compact Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	COPPER
Conductor Size	500 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)