



# Compression Splice

By Burndy  
Catalog # [YS36LFX](#)

500 KCMIL G&H, 444 DLO, 500 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BROWN Color Code, 20 Die Index.



## Application

Wire Splice

### General

Color Code	Brown
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	20
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS
UPC	621945623873

### Dimensions

Dimension - B Length inch	1.31
Length	3.21 in

### Electrical Ratings

Voltage Rating	35 kV
----------------	-------

## Conductor Related

Conductor - Copper DLO Size	444 KCMIL
Conductor - Copper DLO Size Range	444 KCMIL
Conductor - Copper Flex G Size	500 KCMIL
Conductor - Copper Flex G Size Range	500 KCMIL
Conductor - Copper Flex H Size	500 KCMIL
Conductor - Copper Flex H Size Range	500 KCMIL
Conductor - Copper Str Size	500 KCMIL
Conductor - Material	COPPER
Conductor Size	500 KCMIL
Conductor Type	FLEX
Wire Size	500 KCMIL

## Certifications and Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

## Logistics

Carton Quantity	6
-----------------	---

## Product Assets

[Brochures - Burndy\\_Copper Flex Splices - Standard Barrel\\_Brochure](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50117136](#)



A proud member of the Hubbell Family.