



YS38FXLTCKITC, Compression Splice Kit with Clear Heat Shrink, 500 kcmil H,I,K, 550 kcmil G,H,I, 535 DLO Cu

By Burndy
Catalog # YS38FXLTCKITC



500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO CU, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink Pink Color Code, L99 Die Index.

Application

Wire Splice

General

Catalog Number	YS38FXLTCKITC
Color Code	Pink
Color Code - Side A	Pink
Color Code - Side B	Pink
Connector Type	STANDARD BARREL KITS
Die Index	L99
Die Index Run Side	L99
Die Index Tap Side	L99
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810343999
UPC 12 Digit	7818103439999

Dimensions

Dimension - B Length inch	1.77 in
Dimension - L Length Overall mm	109.22 mm
Dimension - Length BB inch	1.77 in
Dimension - Length Overall inch	4.3 in
Dimension - Strip Length inch	1.77

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	535 kcmil
Conductor - Copper Flex G Size A	500 kcmil
Conductor - Copper Flex G Size B	500 kcmil
Conductor - Copper Flex G Size Range	550 kcmil
Conductor - Copper Flex H Size A	500 kcmil
Conductor - Copper Flex H Size B	500 kcmil
Conductor - Copper Flex H Size Range	500 / 550 kcmil
Conductor - Copper Flex I Size A	500 kcmil
Conductor - Copper Flex I Size B	500 kcmil
Conductor - Copper Flex I Size Range	500 / 550 kcmil
Conductor - Copper Flex K Size A	500 kcmil
Conductor - Copper Flex K Size B	500 kcmil
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex M Size A	500 kcmil
Conductor - Copper Flex M Size B	500 kcmil
Conductor - Copper Str Size	500 Kcmil
Conductor - Copper Str Size Range	500 / 550 kcmil
Conductor - Material	COPPER
Conductor Size	500-550 KCMIL
Conductor Type	FLEX
Wire Size	500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

[3D Models - YS38FXLTCKITC_MODEL-PDF](#)
[3D Models - YS38FXLTCKITC_MODEL-IGES](#)
[3D Models - YS38FXLTCKITC_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10101349](#)
[Specifications - YS38FXLTCKITC](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YS38FXLTCKITC-SPEC-EN | REV 8/2024