



Compression Splice

By Burndy
Catalog # [YS38LFX](#)

500 KCMIL H,I,K, 550 KCMIL G,H,I, 535 DLO, 500 AWG CU,
Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C,
Up to 35kV, PINK Color Code, L99 Die Index.



Application

Wire Splice

General

Color Code	Pink
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	L99
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS
UPC	621945624016

Dimensions

Dimension - B Length inch	1.31
Length	3.22 in

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper DLO Size	535 KCMIL
Conductor - Copper DLO Size Range	535 KCMIL
Conductor - Copper Flex G Size	600 KCMIL
Conductor - Copper Flex G Size Range	550 KCMIL
Conductor - Copper Flex H Size	500-550 KCMIL
Conductor - Copper Flex H Size Range	500 - 550 KCMIL
Conductor - Copper Flex I Size	500-550 KCMIL
Conductor - Copper Flex I Size Range	500 - 550 KCMIL
Conductor - Copper Flex K Size	500 KCMIL
Conductor - Copper Flex K Size Range	500 KCMIL
Conductor - Copper Str Size	500-550 KCMIL
Conductor - Material	COPPER
Conductor Size	500-550 KCMIL
Conductor Type	FLEX
Wire Size	500-550 KCMIL

Certifications And Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Brochures - Burndy_Copper Flex Splices - Standard Barrel_Brochure](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50117136](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YS38LFX-SPEC-EN | REV 5/2024

