



Compression Splice

By Burndy
Catalog # YS39A2

AL Splice, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13 oxide inhibitor, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.



Application

Wire Splice

General

Connector Type	DUAL RATED
Die Index	936
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	ALUMINUM
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810095553
UPC 12 Digit	7818100955533

Dimensions

Dimension - B Length fraction	2-7/16 in
Dimension - B Length inch	2.45 in
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.20 in
Dimension - Outside Diameter inch	1.60 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	700 KCMIL- 750 KCMIL
Conductor - AL Str Size Range	700 kcmil-750 kcmil
Conductor - Copper Str Size	700 KCMIL; 750 KCMIL
Conductor - Copper Str Size Range	750 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	700 KCMIL-750 KCMIL
Conductor Type	CODE
Wire Size	700 KCMIL; 750 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 206139](#)



A proud member of the Hubbell Family.