



YS39AM1, Compression Splice, 750 kcmil AL, AL9CU

By Burndy
Catalog # [YS39AM1](#)



AL Splice, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13 oxide inhibitor, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.

Application

Wire Splice

General

Catalog Number	YS39AM1
Color Code	Red
Connector Type	DUAL RATED
Die Index	936
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	ALUMINUM
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Temperature Rating	194
Trade Name	HYLINK™
Type	YS-A
UPC	781810766002
UPC 12 Digit	7818107660022

Dimensions

Dimension - B Length fraction	2-5/8 in
Dimension - B Length inch	2.63 in
Dimension - L Length Overall mm	142 mm
Dimension - Length Overall inch	5.58 in
Dimension - Outside Diameter inch	1.60 in
Dimension - Strip Length inch Length	2-7/8 in 5.58 in
Outside Diameter	1.6 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	700 KCMIL- 750 KCMIL
Conductor - AL Str Size Range	700 kcmil-750 kcmil
Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Compact Size	700;750
Conductor - Copper Str Compact Size Range	700-750
Conductor - Copper Str Size	700 KCMIL; 750 KCMIL
Conductor - Copper Str Size Range	750 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	700 KCMIL-750 KCMIL
Conductor Type	CODE
Wire Size	700 KCMIL; 750 KCMIL

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	2
Minimum Pack Quantity	1

Product Assets

[3D Models - YS39AM1_MODEL-PDF](#)

[3D Models - YS39AM1_MODEL-STEP](#)

[3D Models - YS39AM1_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression](#)

[Connections](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - SD..073942-01](#)

[Specifications - YS39AM1](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YS39AM1-SPEC-EN | REV 8/2024