



YS39AT, Aluminum - Compression Splice

By Burndy
Catalog # YS39AT



High Voltage Uninsulated Al Tube Compression Splice, 700/750 kcmil Al Cable, 8.57" L.

General

Catalog Number	YS39AT
Color Code	Red
Connector Type	Splice
Die Index	301
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Crimps Required	6
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810001424

Dimensions

Dimension - B Length inch	3.69 in
Dimension - L Length Overall mm	218 mm
Dimension - Length Overall inch	8.57 in
Dimension - Outside Diameter inch	1.60 in
Dimension - Pad Width inch	4.18 in
Dimension - Strip Length inch	4 1/2

Conductor Related

Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil
Conductor - AL Str Size Range	700 kcmil-750 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	1440

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YS-AT_LineArt](#)
- [Sales Drawings - SC..025626-01](#)
- [Specifications - YS39AT](#)