

Compression Splice

By Burndy
Catalog # YS39LTCKITC

750 kcmil CU, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink Black Color Code, 23 Die Index.



Application

Wire Splice

General

Color Code	Black
Color Code - Side A	Black
Color Code - Side B	Black
Connector Type	STANDARD BARREL KITS
Die Index	24
Die Index Run Side	24
Die Index Tap Side	24
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810344194
UPC 12 Digit	7818103441944

Dimensions

Dimension - B Length inch	1.67 in
Dimension - L Length Overall mm	104.9 mm
Dimension - Length BB inch	1.67 in
Dimension - Length Overall inch	4.13 in
Dimension - Strip Length inch	1.67

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Str Size B	750
Conductor - Copper Str Size Range	750
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	CODE
Wire Size	750 KCMIL

Certifications and Compliance

Standards - RoHS Compliance Status CM

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	1440

Product Assets

[3D Models - YS39LTCKITC_MODEL-STEP](#)
[3D Models - YS39LTCKITC_MODEL-PDF](#)
[3D Models - YS39LTCKITC_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10101349](#)