

# Compression Splice

By Burndy  
Catalog # YS3CL

3 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated,  
UL/CSA, 90°C, Up to 35kV, WHITE Color Code, 9 Die Index.



## Application

Wire Splice

## General

Color Code	White
Connector Type	STANDARD BARREL
Die Index	9
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810070246
UPC 12 Digit	7818100702466

## Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.05 in
Dimension - Strip Length inch	15/16

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	3 AWG
Conductor - Copper Str Size Range	3 AWG
Conductor - Material	COPPER
Conductor Size	3 AWG
Conductor Type	CODE
Wire Size	#3 AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	46400

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD022390-01](#)