



Compression Splice

By Burndy
Catalog # YS40FX

650 KCMIL G, 646 DLO, 650 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLACK Color Code, 24 Die Index.



Application

Wire Splice

General

Color Code	Black
Connector Type	LONG BARREL
Construction Material - Main	Copper
Die Index	24
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS
UPC	621945624184

Dimensions

Dimension - B Length inch	2.87
Length	6.38 in

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper DLO Size	646 KCMIL
Conductor - Copper DLO Size Range	646 KCMIL
Conductor - Copper Flex G Size	650 KCMIL
Conductor - Copper Flex G Size Range	650 KCMIL
Conductor - Copper Str Size	650 KCMIL
Conductor - Material	COPPER
Conductor Size	650 KCMIL
Conductor Type	FLEX
Wire Size	650 KCMIL

Certifications and Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

Logistics

Carton Quantity	20
Pallet Quantity	1440

Product Assets

[Brochures - Burndy_Copper Flex Splices - Long Barrel_Brochure](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50117138](#)



A proud member of the Hubbell Family.