



# Compression Splice

By Burndy  
Catalog # [YS44FXLTCKITC](#)

750 kcmil G,H,777 DLO CU, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink Yellow Color Code, L115 Die Index.



### Application

Wire Reducing Splice

### General

Color	Yellow
Color Code	Yellow
Color Code - Side A	Yellow
Color Code - Side B	Yellow
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	L115
Die Index Run Side	L115
Die Index Tap Side	L115
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
Type	YS-TC
UPC	781810343951
UPC 12 Digit	7818103439511

### Dimensions

Dimension - B Length inch	1.96 in
Dimension - L Length Overall mm	122.17 mm
Dimension - Length BB inch	1.96 in
Dimension - Length Overall inch	4.81 in
Dimension - Strip Length inch	1.96

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - AL Str Size Range	777 kcmil
Conductor - Copper DLO Size Range	777 kcmil
Conductor - Copper Flex G Size A	750 kcmil
Conductor - Copper Flex G Size B	750 kcmil
Conductor - Copper Flex G Size Range	750 kcmil
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Flex H Size B	750 kcmil
Conductor - Copper Flex H Size Range	750 kcmil
Conductor - Copper Flex I Size A	750 kcmil
Conductor - Copper Flex I Size B	750 kcmil
Conductor - Copper Flex I Size Range	750 kcmil
Conductor - Copper Flex K Size A	750 kcmil
Conductor - Copper Flex K Size B	750 kcmil
Conductor - Copper Flex M Size A	750 kcmil
Conductor - Copper Flex M Size B	750 kcmil
Conductor - Copper Str Size Range	750 Kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	FLEX
Wire Size	750 kcmil G,H,777 DLO

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

## Product Assets

[3D Models - YS44FXLTCKITC\\_MODEL-STEP](#)  
[3D Models - YS44FXLTCKITC\\_MODEL-PDF](#)  
[3D Models - YS44FXLTCKITC\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 10101349](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YS44FXLTCKITC-SPEC-EN | REV 5/2024