



# Compression Splice

By Burndy  
Catalog # [YS44LFX](#)

750 KCMIL G,H,I, 777 DLO, 750 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, YELLOW Color Code, L115 Die Index.



## Application

Wire Splice

## General

Color Code	Yellow
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	L115
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS
UPC	621945623897

## Dimensions

Dimension - B Length inch	1.81
Length	4.28 in

## Electrical Ratings

Voltage Rating	35 kV
----------------	-------

## Conductor Related

Conductor - Copper DLO Size	777 DLO
Conductor - Copper DLO Size Range	777 KCMIL
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper Flex G Size Range	750 KCMIL
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex H Size Range	750 KCMIL
Conductor - Copper Flex I Size	750 KCMIL
Conductor - Copper Flex I Size Range	750 KCMIL
Conductor - Copper Str Size	750 KCMIL
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL

## Certifications and Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

## Logistics

Carton Quantity	4
Pallet Quantity	2304

## Product Assets

[Brochures - Burndy\\_Copper Flex Splices - Standard Barrel\\_Brochure](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50117136](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YS44LFX-SPEC-EN | REV 1/2024