



YS48, Compression Splice, 2000 kcmil Cu, Long Barrel

By Burndy
Catalog # [YS48](#)



2000 kcmil CU, Long Barrel, Internal Chamfer, Tin Plated,
UL/CSA, 90°C, Up to 35kV, BROWN Color Code, 34 Die Index.

Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

General

Catalog Number	YS48
Color Code	Brown
Connector Type	LONG BARREL
Die Index	34
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810527900
UPC 14 Digit GTIN	00781810527900

Dimensions

Dimension - B Length inch	3.27 in
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.57 in
Dimension - Strip Length inch	3-3/8

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper Str Size	2000 kcmil
Conductor - Copper Str Size Range	2000 kcmil
Conductor - Material	COPPER
Conductor Size	2000 KCMIL
Conductor Type	CODE
Wire Size	2000 kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	3
Minimum Pack Quantity	3
Pallet Quantity	588

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD007774-01](#)
[Specifications - YS48](#)