



YS4CFXLTCKITC, Compression Splice Kit with Clear Heat Shrink, 4 Flex G,H,I,K,M, DLO, 4 AWG Cu

By Burndy
Catalog # YS4CFXLTCKITC



4 Flex G,H,I,K,M,DLO, 4 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink Gray Color Code, 8 Die Index.

Application

Wire Splice

General

Catalog Number	YS4CFXLTCKITC
Color Code	Gray
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	8
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
Type	YS-TC
UPC	781810346402
UPC 12 Digit	7818103464022

Dimensions

Dimension - B Length inch	0.74 in
Dimension - L Length Overall mm	42.92 mm
Dimension - Length BB inch	0.74 in
Dimension - Length Overall inch	1.69 in
Dimension - Strip Length inch	11/16

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Flex M Size Range	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	12
Pallet Quantity	3600

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression](#)

[Connections](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 10101349](#)

[Specifications - YS4CFXLTKITC](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YS4CFXLTKITC-SPEC-EN | REV 8/2024