



YS6CFXLTKITC, Compression Splice Kit with Clear Heat Shrink, 6 Flex G,H,I,K,M, DLO, 6 AWG, Cu

By Burndy
Catalog # [YS6CFXLTKITC](#)

6 Flex G,H,I,K,M,DLO, 6 AWG, CU, SPLICE KIT with Clear Heat Shrink

Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex K Size A	6 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex M Size A	6 AWG
Conductor - Copper Flex M Size B	6 AWG
Conductor - Copper Flex M Size B	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Flex I Size B	6 AWG



Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex G Size A	6 AWG
Conductor - Copper Flex G Size B	6 AWG
Conductor - Copper DLO Size Range	6 AWG
Conductor - Copper DLO Size	6 AWG
Conductor Size	6 AWG
Conductor - Copper Flex H Size A	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex G Size Range	6 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Size B	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size A	6 AWG
Conductor - Copper Flex I Size	6 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40.64 mm
Dimension - Strip Length inch	0.70 in
Dimension - B Length inch	0.73 in
Dimension - Length BB inch	0.73 in

Dimension - Length Overall inch	1.6 in	Finish Type	Tin-Plated
		UPC 12 Digit	781810346457
		UPC 14 Digit GTIN	00781810346457
General		Logistics	
Trade Name	HYLINK™	Minimum Pack Quantity	25
Die Index	7	Pallet Quantity	2250
Feature - Barrel Type	Standard	Carton Quantity	25
Plated	N		
Color Code	Blue		
UPC	781810346457		
Type	YS-TC		
Construction Material - Main	Copper	Operational	
Material	Copper	Temperature Rating	194
Plating Type	Unplated	Product Assets	

[Catalog \[English\]](#)



A Hubbell brand