

## YS6CLBOX, Cu Compression Splice, Standard Barrel, 6 AWG

By Burndy  
Catalog # [YS6CLBOX](#)

6 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated,  
UL/CSA, 90°C, Up to 35kV, BLUE Color Code, 7 or 374 Die Index



### Application

Wire Splice

### General

Catalog Number	YS6CLBOX
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	7
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810555750
UPC 12 Digit	7818105557500

### Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Strip Length inch	7/8

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE
Wire Size	#6 AWG

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1

### Product Assets

- [3D Models - YS6CLBOX\\_MODEL-PDF](#)
- [3D Models - YS6CLBOX\\_MODEL-STEP](#)
- [3D Models - YS6CLBOX\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd022390\\_1](#)
- [Specifications - YS6CLBOX](#)



A Hubbell brand