

# Compression Splice

By Burndy  
Catalog # YS8CFXB

DISCONTINUED BY YS8C.



## Application

Wire Splice

## General

Color Code	Red
Connector Type	LONG BARREL
Die Index	49
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810082904
UPC 12 Digit	7818100829044

## Dimensions

Dimension - B Length inch	0.90 in
Dimension - D inch	0.32 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	1.99 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Strip Length inch	1 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	8 AWG
Conductor - Copper DLO Size Range	8 AWG
Conductor - Copper Flex G Size	8 AWG
Conductor - Copper Flex G Size Range	8 AWG
Conductor - Copper Flex H Size	8 AWG
Conductor - Copper Flex H Size Range	8 AWG
Conductor - Copper Flex I Size	8 AWG
Conductor - Copper Flex I Size Range	8 AWG
Conductor - Copper Flex K Size	8 AWG
Conductor - Copper Flex K Size Range	8 AWG
Conductor - Copper Flex M Size	8 AWG
Conductor - Copper Solid Size	8 AWG
Conductor - Copper Solid Size Range	8 AWG
Conductor - Copper Str Navy Size	23 (7)
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG
Conductor - Material	COPPER
Conductor Size	8 AWG
Conductor Type	CODE/FLEX
Wire Size	8 AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity 50

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - SE208037-01\\_F](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YS8CFXB-SPEC-EN | REV 5/2024