

YSA25R2N, Disconnectable Terminal with Slotted Pad

By Burndy
Catalog # [YSA25R2N](#)



DISCONNECTABLE TERMINAL(WITH SLOTTED PAD).

General

Catalog Number	YSA25R2N
Connector Type	Terminal
Die Index	659;C
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810017081
UPC 12 Digit	7818100170811

Dimensions

Dimension - B Length inch	1.64 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	6.25 in
Dimension - Outside Diameter inch	0.80 in
Dimension - Pad Width inch	1.90 in
Dimension - Thread Size	1/2
Thickness - Pad	0.38 in

Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YSA-R-2N_LineArt](#)
[Sales Drawings - sd051201-01](#)
[Specifications - YSA25R2N](#)