



## YSA321R2N, Disconnectable Terminal with Slotted Pad

By Burndy  
Catalog # [YSA321R2N](#)



DISCONNECTABLE TERMINAL(WITH SLOTTED PAD).

### General

Connector Type	Terminal
Die Index	317;M
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810017135
UPC 12 Digit	7818100171355

### Dimensions

Dimension - B Length inch	3.06 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.71 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.90 in
Dimension - Thread Size	1/2
Thickness - Pad	0.38 in

### Conductor Related

Conductor - ACSR Str Size	300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	350 kcmil
Conductor - Copper Str Size	350 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	3
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd051201-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YSA321R2N-SPEC-EN | REV 8/2023