



YSA37R2N, Disconnectable Terminal with Slotted Pad

By Burndy
Catalog # [YSA37R2N](#)



DISCONNECTABLE TERMINAL(WITH SLOTTED PAD).

General

Connector Type	Terminal
Die Index	M
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810017128
UPC 12 Digit	7818100171288

Dimensions

Dimension - B Length inch	3.06 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	200 mm
Dimension - Length Overall inch	7.84 in
Dimension - Outside Diameter inch	1.36 in
Dimension - Pad Width inch	1.90 in
Thickness - Pad	0.38 in

Conductor Related

Conductor - ACSR Str Size	477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker kcmil-477. (30/7) Hen kcmil
Conductor - AL Str Size	556 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd051201-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSA37R2N-SPEC-EN | REV 8/2023