

Compression Splice

By Burndy
Catalog # YSCM167

134,340 - 166,560 Circular Mils, CU, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, Orange Color Code, 14 Die Index.



Application

Wire Splice

General

Color Code	Orange
Connector Type	Splice
Die Index	14
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSCM
UPC	781810358566
UPC 12 Digit	7818103585666

Dimensions

Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.81 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Strip Length inch	1-1/16

Electrical Ratings

Voltage - Maximum	600 V
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Material	COPPER
Conductor Size	134,340-166,560 CMILS
Conductor Type	CODE
Wire Range	134,340 - 166,560 Circular Mils

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	200
Minimum Pack Quantity	1
Pallet Quantity	46400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094201](#)