

# Compression Splice

By Burndy  
Catalog # YSCM212

167,380 - 211,820 Circular Mils, CU, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, Purple Color Code, 15 Die Index.



## Application

Wire Splice

## General

Color Code	Purple
Connector Type	Splice
Die Index	15
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSCM
UPC	781810358573
UPC 12 Digit	7818103585733

## Dimensions

Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in
Dimension - Outside Diameter inch	0.78 in
Dimension - Strip Length inch	1-1/16

## Electrical Ratings

Voltage - Maximum	600 V
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG
Conductor - Material	COPPER
Conductor Size	167,380-211,820 CMILS
Conductor Type	CODE
Wire Range	167,380 - 211,820 Circular Mils

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	200
Minimum Pack Quantity	1
Pallet Quantity	37000

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094201](#)