

Compression Splice

By Burndy
Catalog # YSCM231

230,800 - 230,800 Circular Mils, CU, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, Yellow Color Code, 16 Die Index.



Application

Wire Splice

General

Color Code	Yellow
Connector Type	Splice
Die Index	16
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	Type YSCM
UPC	781810363287
UPC 12 Digit	7818103632877

Dimensions

Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.05 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Strip Length inch	1-1/16

Electrical Ratings

Voltage - Maximum	35000 V
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Material	COPPER
Conductor Size	230,800-230,800 CMILS
Conductor Type	CODE
Wire Range	230,800 - 230,800 Circular Mils

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	29000

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094201](#)