



YSCM27, Seamless Parallel Compression Splice Connector, 16,910-26,890 Circular Mils CU

By Burndy
Catalog # YSCM27



16,910 - 26,890 Circular Mils, CU, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, Blue Color Code, 7 Die Index.

Application

Wire Splice

General

Catalog Number	YSCM27
Color Code	Blue
Connector Type	Splice
Die Index	7
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSCM
UPC	781810358504
UPC 12 Digit	7818103585044

Dimensions

Dimension - L Length Overall mm	13 mm
Dimension - Length Overall inch	0.50 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Strip Length inch	11/16

Electrical Ratings

Voltage - Maximum	600 V
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	7 AWG;6 AWG
Conductor - Copper Str Size Range	7 AWG-6 AWG
Conductor - Material	COPPER
Conductor Size	16,910-26,890 CMILS
Conductor Type	CODE
Wire Range	16,910 - 26,890 Circular Mils

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	200
Minimum Pack Quantity	200
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094201](#)
[Specifications - YSCM27](#)



A Hubbell brand