



YSD25R2R, Aluminum Splice

By Burndy
Catalog # YSD25R2R

Al LINKIT Compression Splice, 1/0 AWG ACSR, 1/0 Str. Al/Cu, 2/0 AWG Al Compt(SideA), #2 AWG ACSR, #1 - #2 Str. Al/Cu, 1/0 AWG Al Compt(Side B).



General

Color Code - Side A	Yellow
Color Code - Side B	Red
Die Index	249;840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810195086
UPC 12 Digit	7818101950866

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	1/0 AWG
Conductor - ACSR Str Size B	2/0 AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	1 AWG, 2 AWG
Conductor - AL Str Size B Range	1 AWG-2 AWG
Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	1 AWG, 2 AWG
Conductor - Copper Str Size B Range	1 AWG- 2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7400

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd046623-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSD25R2R-SPEC-EN | REV 8/2023