



YSD26R2R, Aluminum Sleeve with Solid Center Barrier

By Burndy
Catalog # [YSD26R2R](#)



Aluminum compression sleeve with solid center barrier, Designed for commercial and heavy residential services.

General

Color Code - Side A	Gray
Color Code - Side B	Red
Die Index	249;K-840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810144008
UPC 12 Digit	7818101440088

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size B	4/0 AWG
Conductor - AL Str Size A	2/0 AWG
Conductor - AL Str Size B	2 AWG, 3 AWG, 4 AWG
Conductor - AL Str Size B Range	2 AWG-4 AWG
Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Str Size B	2 AWG, 3 AWG, 4 AWG
Conductor - Copper Str Size B Range	2 AWG-4 Awg

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[3D Models - YSD26R2R_MODEL-STEP](#)
[3D Models - YSD26R2R_MODEL-PDF](#)
[3D Models - YSD26R2R_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd046623-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSD26R2R-SPEC-EN | REV 8/2023