



YSD27R25R, Aluminum Sleeve with Solid Center Barrier

By Burndy
Catalog # [YSD27R25R](#)



AL compression sleeve with solid center barrier, Designed for commercial and heavy residential services, Color Code: Black (Side A), Yellow (Side B).

General

Color Code - Side A	Black
Color Code - Side B	Yellow
Die Index	249;K-840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810145104
UPC 12 Digit	7818101451044

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size B	1/0 (6/1) Raven AWG
Conductor - AL Str Size A	3/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - Copper Str Size A	3/0 AWG
Conductor - Copper Str Size B	1/ AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7400

Product Assets

- [3D Models - YSD27R25R_MODEL-IGES](#)
- [3D Models - YSD27R25R_MODEL-PDF](#)
- [3D Models - YSD27R25R_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_YSD_LineArt](#)
- [Sales Drawings - sd046623-01](#)



A proud member of the Hubbell Family.