



YSD28R25RBOX100, Aluminum LINKIT Splice, 100 piece box

By Burndy
Catalog # [YSD28R25RBOX100](#)



Al LINKIT Splice Box, 4/0 AWG ACSR/Al/Cu, 300 kcmil Al Comp.(Side A), 1/0 AWG ACSR/Al/Cu, 2/0 AWG Al Comp.(Side B).

General

Catalog Number	YSD28R25RBOX100
Color Code - Side A	Pink
Color Code - Side B	Yellow
Die Index	249;840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810047064
UPC 12 Digit	7818100470644

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	4/0 AWG
Conductor - ACSR Str Size B	1/0 Awg
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	9000

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd046623-02](#)
- [Specifications - YSD28R25RBOX100](#)