



YSD28R2W, Aluminum Sleeve with Solid Center Barrier

By Burndy
Catalog # [YSD28R2W](#)



AL compression sleeve with solid center barrier, Designed for commercial and heavy residential services, Color Code: Pink (Side A), Orange (Side B).

General

Color Code - Side A	Pink
Color Code - Side B	Orange
Die Index	249;K-840
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810146057
UPC 12 Digit	7818101460577

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size B	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size B	4 AWG;3 AWG;2 AWG
Conductor - AL Str Size B Range	4 AWG-2 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size B Range	4 AWG-2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YSD_LineArt](#)
[Sales Drawings - sd046623-02](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YSD28R2W-SPEC-EN | REV 5/2024