


Nylon Splice For 12 - 10 AWG

By Burndy
Catalog # YSE10BOX



Nylon Splice For 12 - 10 AWG.

Application

For Splicing Aircraft And Commercial Flexible Cables

General

Color Code	Yellow
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Temperature Rating	105
Trade Name	INSULINK™
Type	YSE
UPC	781810566305
UPC 12 Digit	7818105663055

Dimensions

Cable Insulation Diameter Maximum	0.209 in
Dimension - B Length fraction	3/10 in
Dimension - B Length inch	0.30 in
Dimension - Diameter Max Size inch	0.22 in
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.15 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Strip Length inch	23/64 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12-10
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094194](#)

