

YSH3939 Compression H-Tap Connector

By Burndy
Catalog # [YSH3939](#)



Copper Split Compression Wye Tap Connector, 750-350 (550-500) (Tap), Provides maximum design and installation flexibility.

Features

- Accommodates a wide range of Run/Tap Copper cable combinations including both flexible and code combinations allowing maximum flexibility
- Tap grooves function independently from each other, use of one tap is required, balance may be used or left empty

Application

For High Voltage (15 KV) Power Cables With Copper Conductors

General

Catalog Number	YSH3939
Color Code	Yellow
Connector Type	H-Tap
Die Index	KR
EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	Taps
UPC	781810036983
UPC 14 Digit GTIN	00781810036983

Dimensions

Dimension - Height inch	2.97 in
Dimension - Height mm	75.4 mm
Dimension - Length Overall inch	3.00 in
Dimension - Strip Length inch	1 1/2
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

Conductor Related

Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Run Range	500-750 kcmil
Conductor - Copper Str Tap	350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Tap Range	350 kcmil-750 kcmil

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1200

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YSH_LineArt](#)
[Sales Drawings - 20880601](#)
[Specifications - YSH3939](#)