

Uninsulated Parallel Splice For 800 kcmil

By Burndy
Catalog # [YSM40L144](#)



Uninsulated Parallel Splice For 800 kcmil.

Application

Splicing

General

Connector Type	Parallel Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	SPLICE CONNECTOR
Trade Name	HYLINK™
Type	Splice
UPC	781810371145
UPC 12 Digit	7818103711455

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Inside Diameter inch	1.03 in
Dimension - Length Overall inch	1.48 in
Dimension - Outside Diameter inch	1.35 in

Conductor Related

Conductor - Copper Str Compact Size	800 kcmil
Conductor - Copper Str Compact Size Range	800 kcmil
Conductor - Copper Str Size	800 kcmil
Conductor - Copper Str Size Range	800 kcmil
Conductor Size	800 KCMIL
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10043626-01](#)