



## YSR28FX26FXLTCKITC, Compression Splice Reducer, Barrel A 4/0 Flex, Barrel B 2/0 Flex, includes clear heat shrink

By Burndy  
Catalog # YSR28FX26FXLTCKITC



CU Splice Reducer, Barrel A 4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, Barrel B 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Purple/Black Color Code, 15/13 Die Index.

### Application

Wire Reducing Splice

### General

Catalog Number	YSR28FX26FXLTCKITC
Color Code	Purple, Black
Color Code - Side A	Purple
Color Code - Side B	Black
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	15/13
Die Index - Element A	15
Die Index - Element B	13
Die Index Run Side	15
Die Index Tap Side	13
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810434376
UPC 12 Digit	7818104343766

### Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.43 in
Dimension - L Length Overall mm	75 mm
Dimension - Length BB inch	1.13 in
Dimension - Length Overall inch	2.94 in
Dimension - Strip Length inch	1.36 in

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Run	4/0 AWG
Conductor - Copper Flex G Size	4/0 AWG
A	
Conductor - Copper Flex G Size	2/0 AWG
B	
Conductor - Copper Flex G Tap	2/0 AWG
Conductor - Copper Flex H Run	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
A	
Conductor - Copper Flex H Size	2/0 AWG
B	
Conductor - Copper Flex H Tap	2/0 AWG
Conductor - Copper Flex I Run	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
A	
Conductor - Copper Flex I Size	2/0 AWG
B	
Conductor - Copper Flex I Tap	2/0 AWG
Conductor - Copper Flex K Run	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
A	
Conductor - Copper Flex K Size	2/0 AWG
B	
Conductor - Copper Flex K Tap	2/0 AWG
Conductor - Copper Flex M Run	4/0 AWG
Conductor - Copper Flex M	4/0 AWG
Size A	
Conductor - Copper Flex M	2/0 AWG
Size B	
Conductor - Copper Flex M Tap	2/0 AWG
Conductor - Copper Str Size	4/0 AWG-2/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG-2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	4/0 AWG-2/0 AWG

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	12
Minimum Pack Quantity	12
Pallet Quantity	1080

## Product Assets

[3D Models - YSR28FX26FXLTCKITC\\_MODEL-PDF](#)  
[3D Models - YSR28FX26FXLTCKITC\\_MODEL-IGES](#)  
[3D Models - YSR28FX26FXLTCKITC\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - SPLICE KIT trilingual](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10021428](#)  
[Specifications - YSR28FX26FXLTCKITC](#)



A Hubbell brand