



YSR28FX26FXLTCKITC, Compression Splice Reducer, Barrel A 4/0 Flex, Barrel B 2/0 Flex, includes clear heat shrink

By Burndy

Catalog # [YSR28FX26FXLTCKITC](#)

CU Splice Reducer, Barrel A 4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, Barrel B 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Purple/Black Color Code, 15/13 Die Index.

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

General

Catalog Number	YSR28FX26FXLTCKITC
Color Code	Purple, Black
Color Code - Side A	Purple
Color Code - Side B	Black
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	15/13
Die Index - Element A	15
Die Index - Element B	13
Die Index Run Side	15
Die Index Tap Side	13
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	YSR-TC



UPC	781810434376
UPC 12 Digit	7818104343766

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.43 in
Dimension - L Length Overall mm	75 mm
Dimension - Length BB inch	1.13 in
Dimension - Length Overall inch	2.94 in
Dimension - Strip Length inch	1.36 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	4/0 AWG
Conductor - Copper Flex G Size A	4/0 AWG
Conductor - Copper Flex G Size B	2/0 AWG
Conductor - Copper Flex G Tap	2/0 AWG
Conductor - Copper Flex H Run	4/0 AWG
Conductor - Copper Flex H Size A	4/0 AWG
Conductor - Copper Flex H Size B	2/0 AWG
Conductor - Copper Flex H Tap	2/0 AWG
Conductor - Copper Flex I Run	4/0 AWG
Conductor - Copper Flex I Size A	4/0 AWG
Conductor - Copper Flex I Size B	2/0 AWG
Conductor - Copper Flex I Tap	2/0 AWG
Conductor - Copper Flex K Run	4/0 AWG

Conductor - Copper Flex K Size A	4/0 AWG
Conductor - Copper Flex K Size B	2/0 AWG
Conductor - Copper Flex K Tap	2/0 AWG
Conductor - Copper Flex M Run	4/0 AWG
Conductor - Copper Flex M Size A	4/0 AWG
Conductor - Copper Flex M Size B	2/0 AWG
Conductor - Copper Flex M Tap	2/0 AWG
Conductor - Copper Str Size	4/0 AWG-2/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG-2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	4/0 AWG-2/0 AWG

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	12
Pallet Quantity	1080

Product Assets

- [3D Models - YSR28FX26FXLTCKITC_MODEL-IGES](#)
- [3D Models - YSR28FX26FXLTCKITC_MODEL-PDF](#)
- [3D Models - YSR28FX26FXLTCKITC_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SPLICE KIT trilingual](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10021428](#)
- [Specifications - YSR28FX26FXLTCKITC](#)

